

# Chemiluminescence Ammonia and nitrogen oxides analyzer

AIR QUALITY MONITORING SYSTEMS



### SPECIFIC FEATURES:

- Combines the AC32e chemiluminescence analyzer with the external NH<sub>3</sub>→NO thermal converter module CNH3 for stable and repeatable multi-gas measurements at very low levels
- Selectable and independent NO, NO<sub>2</sub>, NOx, NH<sub>3</sub> ranges
- User programmable ranges and average time
- Excellent metrological performances
- Innovative conception for excellent sensitivity and signal stability
- Includes embedded Communication Protocol for XR<sup>®</sup> Software with automatic recognition & configuration
- Ultra low power consumption: an environment-friendly and cost-saving analyzer
- Breakthrough mechanical design for weight and power saving as well as thermal insulation & reliability
- Automatic recognition of plugged electronic boards or optional devices: plug & play principle
- Local and remote control through digital port (configuration, calibration, test and diagnostic parameters for maintenance support)
- Real-time calibration graph, animated synoptic, auto-diagnostic, control and maintenance data screens can be displayed while the instrument is operating
- Service assistance inside: detects early signs of trouble, allows predictive maintenance, identifies the needed service and guides service operations step by step: increased productivity on site, reduced downtime, more efficiency, less training

### MAIN APPLICATIONS:

- > Leak detection and monitoring of fugitive emissions: quarries, storage facilities, mines, fertilizers plants
- > Odor monitoring: WWTP, recycling, pulp and paper manufacturing, composting...
- >Low level ammonia monitoring in ambient air

#### **4 SELECTABLE MODES:**

- Continuous NH<sub>3</sub>
- Continuous NO/ NO<sub>2</sub> / NH<sub>3</sub>
- Continuous NO/ NO<sub>2</sub>
- Continuous NO

### The AC32e offers compliance with:

ISO 7996, EN 14211 (2012), EN 15267 (2009), 40 CFR part 53 & part 58





www.envea.global

U.S. EPA APPROVED RFNA-0118-249

# Ammonia and Nitrogen Oxides Analyzer AC32e синз

### PRINCIPLE OF OPERATION:

The AC32e-CNH3 consisits of 2 associated elements: the  $NH_3 \rightarrow NO$  module (ref CNH3-S2) plus the NOx analyzer (ref AC32e)

TECHNICAL SPECIFICATIONS - AC32e		
Measurement Range	0-1 ppm / 0-10 ppm (user selectable or auto-ranging)	
Measured parameter	NO, NO <sub>2</sub> & NOx	
Detection limit (2σ)	<0.2 ppb	
Noise	<0.1 ppb	
Zero drift	<1 ppb / 24h	
Span drift	<1 ppb / 7 days	
Response time	min. 40 s	
Linearity	1% (of F.S.)	
Repeatability	1%	
Sample flow-rate	0.33 l/min	
Memory Capacity	1 year (15 minutes average)	
Output connectivity	Ethernet (RJ45 socket, UDP protocol, Modbus TCP), USB port, External zero/ span SV control	
Dimensions L x W x H (mm)	483 x 545 x 133	
Chassis	19" rack, 3U	
Weight	10 kg without external pump (4.5 kg)	
Standard operating temperature	0°C to +40°C	
Power supply	100-250 V, 50/60 Hz	
Power consumption	160 VA (average) 250 VA (peak)	
Chamber pressure	200 hPa	
NOx converter	Molybdenum (regulated at 340°C)	
Ozone scrubber	Heated catalytic	
P.M temperature	controlled at 0°C	
Reaction chamber temperature	60°C	
Filter valve block for calibration control (zero & span)		
Integrated web-server with full remote emulation of the analyzer		

Pressure and temperature compensation

#### **TECHNICAL SPECIFICATIONS - CNH3 MODULE** Measurement Range 0.10 /0.25 /0.5 /1 ppm (user selectable ranges) Measured parameter $NH_{z}$ Lower detectable limit $(2\sigma)$ 0.001 ppm NH<sub>3</sub> to NO converter Quartz, 980°C Output connectivity Ethernet network connection (RJ45) Dimensions $L \times D \times H$ (mm) 483 x 545 x 133 **Operating temperature** +10°C to +35°C

Weight	7 kg for the 230V version 9.6 kg for the 110V version
Power supply	115 V, 60 Hz - 230 V, 50 Hz
Power consumption	160VA
Digital output	RS 232 or RS 422 port

## MAIN OPTIONS:

#### for the AC32e:

- 7" TFT color touch screen on the AC32e
- WiFi module (in standard with the no-screen version)
- RS232 or RS485 serial interface (via USB port)
- Built-in permeation bench with NO<sub>2</sub> tube
- Sample dryer
- External opto-isolated I/O interface with:
  4 independent analog inputs
  - 4 independent analog outputs
  - 4 remote control inputs
  - 6 dry contacts outputs
- 24V power supply interface & enhanced T° range for utilization without air conditioner

### for the CNH3 module:

- a solenoid valve (NH3 SV)
- rear pannel to be equipped with 2 additional bulkhead unions
- a communication cable







